

workshop: DS BERGEN AS		person:	Daniel Kristensen
street: Storebotn 55G		phone:	91649162
place: 5309 Klippepestø		fax:	
		email:	Daniel@dsbergen.no
customer: Sjøentreprenøren AS		person:	Ingnar Aune
street:		phone:	
place: Bergen		fax:	
		email:	ingnar.aune@ncc.no
device data:	deadlines:	device-info:	service:
device no: 14	1 y test 23.02.2027 1 y srv 23.02.2027		- 1 year service
type: Interspiro Spiromatic Mask			
class: mask PP			
location: Mjø			

fire set Chamber control

tests/measurements	unit	min	max	actual	result
visual test (0 = ok) input mask: (0 = classic, > 0 = extended/list...)			0	0	OK
mask fitted approx. 6 sec head expansion Mask volume 0,2 l				0	OK
leakage test w open exhalation valve 0,25 min at p=-10 nbar	nbar		7,5	-0,8	OK
opening pressure of the outlet valve at 10 l/min suction	nbar	4,2	8	4,8	OK

test executed: 23.02.2026 10:04
by: Daniel Kristensen

test signed: 23.02.2026 10:05
by: Daniel Kristensen

LabNet V: 2025.12.2.0

next test on: 23.02.2027

result:

device ready for use

workshop: DS BERGEN AS		person:	Daniel Kristensen
street: Storebotn 55G		phone:	91649162
place: 5309 Klippestø		fax:	
		email:	Daniel@dsbergen.no
customer: Sjøentreprenøren AS		person:	Ingnar Aune
street:		phone:	
place: Bergen		fax:	
		email:	ingnar.aune@ncc.no
device data:	deadlines:	device-info:	service:
device no: 1102203L	1 y test 23.02.2027 1 y srv 23.02.2027		1 year service
type: Interspiro LA Spiromatic 400 PE/ESA			
class: demand valve overpressure			
location: Mjø			

fire set Chamber control

tests/measurements	unit	min	max	actual	result
visual test (0 = ok) input mask: (0 = classic, > 0 = extended/list...)			0	0	OK
static positive pressure at bar cylinder pressure, suction 0=yes 1=no	nbar	1,5	3,9	2,1	OK
inhalation resistance at 40 x 2,5 l/min hubs HP .>. bar	nbar	0,1	12,5	1,4	OK

test executed: 23.02.2026 10:04
 by: Daniel Kristensen
 test signed: 23.02.2026 10:05
 by: Daniel Kristensen

result:
 device ready for use

LabNet V: 2025.12.2.0

next test on: 23.02.2027

workshop: DS BERGEN AS		person:	Daniel Kristensen
street: Storebotn 55G		phone:	91649162
place: 5309 Klippepestø		fax:	
		email:	Daniel@dsbergen.no
customer: Sjøentreprenøren AS		person:	Ingnar Aune
street:		phone:	
place: Bergen		fax:	
		email:	ingnar.aune@ncc.no
device data:	deadlines:	device-info:	service:
device no: 1103012L	1 y test 23.02.2027 1 y srv 23.02.2027		1 year service
type: Interspiro Spiromatic 90			
class: SCBA Basic device			
location: Mjø			

fire set Chamber control

tests/measurements	unit	min	max	actual	result
visual test (0 = ok) input mask: (0 = classic, > 0 = extended/list...)			0	0	OK
static medium pressure at 200 bar cylinder pressure	bar	6,5	10,5	8,3	OK
MP leakage after 0,5 min at 200 bar, limit 1 [0=rel 1=abs], pulse	bar		10,5	8,5	OK
warning signal response pressure -speed 10 (0..20)	bar	50	60	53	OK
dynamic medium pressure at 25 x 2 l/min breathing 0=abs. 1=rel.	bar	6,5	8,5	7,6	OK
High-pressure leak test, test time: 0,5 min, test pressure: bar	bar	-5		0	OK
pressure comparison at 200 bar	bar	-10	10	2	OK
pressure comparison at 100 bar	bar	-10	10	2	OK
pressure comparison at 70 bar	bar	-5,8	5,8	3	OK
pressure release of test equipment (HP, MP and LP)				0	OK

test executed: 23.02.2026 10:04
 by: Daniel Kristensen
 test signed: 23.02.2026 10:05
 by: Daniel Kristensen

result:

device ready for use

LabNet V: 2025.12.2.0

next test on: 23.02.2027